



THERMAL DYNAMICS®

AUTOMATION

Introducing

SpeedLok™

The new, rapid locking XT™-300 Series torch from Thermal Dynamics.

- **Rapid Cartridge Installation**
- **180° (1/2 Turn) Engagement**
- **Positive Locking Action**
- **Convenient Position Indicators**
- **Assured O-Ring Seating**
- **Existing Cartridge Easily Adaptable***



XT-300 Plasma Torch with SpeedLok Technology

The **SpeedLok** retaining ring accelerates the installation of the consumables cartridge onto the XT-300 Series torch body. The new design eliminates the torch head threads thus assuring the seating of the O-rings. Simply align the indicator marks on the retaining ring with the torch body, slide the cartridge on and turn 180 degrees. The cartridge automatically locks and seats onto the torch body. Existing cartridges can easily be adapted by simply replacing with a new **SpeedLok** retaining ring. It's that simple!.



Torch Body with SpeedLok Design

Consumables Cartridge with SpeedLok Retaining Ring

For further information contact your local Thermal Dynamics representative.

***Requires Replacement Retaining Ring (9-9489)**